



# TSU-C/D

Ice thermal storage

# 790D-1440D

Engineering data

**REMARK:** Do not use for construction. Refer to factory certified dimensions & weights. This page includes data current at time of publication, which should be reconfirmed at the time of purchase. In the interest of product improvement, specifications, weights and dimensions are subject to change without notice.

## General notes

1. All dimensions are in mm. Weights are in kg.
2. Unit should be continuously supported on a flat level surface.
3.  $H_1$  = installed height. Coils connections are closed and filled with inert gas for shipping and storage. Add 130 mm for shipping height.
4. Refrigerant charge listed is operating charge for pump recirculated bottom feed. For other feed systems, consult your BAC representative.

**Last update:** 02/05/2024

**TSU-C/D 790D-1440D**



1. Coil connections; 2. Make up ND50; 3. Overflow ND50; 4. Water out; 5. Water in; 6. Drain ND50; 7. ICE LOGIC®.



Model	Approx. Ship. Weight (kg)	Approx. Oper. Weight (kg)	Air Pump (kW)	Water Volume (l)	Pull Down Volume (l)	Coil Volume (L)	R717 charge (kg)	Water Conn. In ND (mm)	Water Conn. Out ND (mm)	H	H1	L	W
TSU-790D	1397 5	6863 5	2,5	5186 0	1510	2750	1187	200+ 2x80	200	2415	2575	7290	3582
TSU-940D	1568 0	7959 0	2,5	6057 0	1630	3115	1345	200+ 2x80	200	2415	2575	8509	3582
TSU-1080 D	1815 0	9150 0	2,5	6965 0	1780	3455	1492	200+ 2x80	200	2415	2575	9703	3582
TSU-1220 D	1980 0	1032 20	4,0	7836 0	1890	3795	1638	200+ 2x80	200	2415	2575	1092 2	3582
TSU-1440 D	2237 0	1192 20	4,0	9123 0	2230	4330	1869	200+ 2x80	200	2415	2575	1272 5	3582